




The illustrations below are intended to be examples of the varied ways in which **Connectorail®**, **Carlstadt®** and Traditional Railing components may be combined.

SURFACE-MOUNTED




- 1** Handrail moulding: **6939**
 Post: **427**
 Post bracket: **442**
 Cover flange: **777**
- 2** Handrail moulding:
5235 with $1\frac{1}{2}'' \times \frac{1}{2}'' \times \frac{1}{8}''$
Nickel-Silver channel
 Post: **1334**
 Post cap: **1334N**
 Post bracket: **1341**
 Panel clips: **413**
 Cover flange: **1374**
 Panel: by others
- 3** Handrail moulding: **6530**
 Bracket: **171**
 Post: **6423**
 Support bar: **6540**
 Cover flange: **773**
 Glass framing:
8106, 8107, and 8708
 Panel: by others

- 4** Handrail moulding:
 $1\frac{1}{2}''$ sch. **40 Aluminum** pipe
 Bracket: **161**
 Post: **6430**
 Cover flange: **435**
 Reinforcing bar: **436E**
- 5** Handrail mouldings: **6503** and
 $1\frac{1}{4}''$ sch. **40 Stainless** pipe
 Brackets: **241** and **222**
 Anchor plug: **238**
 Post: $1'' \times 1\frac{1}{2}''$ **Stainless** tubing
 Post cap: **231**
 Reinforcing bar: **294**
 Cover flange: **237**
- 6** Handrail mouldings:
4575 with $1\frac{1}{2}'' \times \frac{1}{2}'' \times \frac{1}{8}''$
Bronze channel and **6488**
 Brackets: **841** and **896**
 Post: **4830**
 Post cap: **831**
 Reinforcing bar: **436E**

- Cover flange: **835**
 Anchor plug: **432**
- 7** Handrail mouldings: **6502** and
 $1\frac{1}{4}''$ sch. **5 Stainless** pipe
 Bracket: **207**
 Post bracket: **222**
 Post: $1\frac{1}{2}''$ sch. **5 Stainless** pipe
 Post bracket adapter: **9361**
 Reinforcing bar: **9392**
 Cover flange: **211**
 Anchor plug: **9362**
- 8** Handrail moulding:
 $1\frac{1}{2}''$ sch. **40 Aluminum** pipe
 Post bracket: **322**
 Post: **7504**
 Post cap: **7580**
 Post bracket adapter: **7261**
 Heavy-duty floor flange: **7571**
 Anchor plug: **7562**

The illustrations below are intended to be examples of the varied ways in which Connectorail®, Carlstadt® and Traditional Railing components may be combined.

FASCIA-MOUNTED



- 9** Handrail moulding: 6935 with Aluminum channel 1 1/2" x 1/2" x 1/8"
Post bracket: 312
Post: 424
Fascia flange: 408
Panel framing: 8106, 8107 and 8708
Panel: by others
- 10** Handrail moulding: 6405
Post brackets: 439 and 151
Post: 430
Upper post cap: 431
Lower post cap: 433
Post bracket anchor plug: 432
Fascia bracket: 428
- 11** Handrail mouldings: 6502 and 1 1/4" sch. 40 Stainless pipe

- Post brackets: 241 and 222
Anchor plug: 238
Post: 230
Upper post cap: 231
Anchor bar with lower post cap: 233B with Stainless post cap
Fascia bracket: 228
Post Anchor: 227
- 12** Handrail moulding: 4572
Post bracket: 841
Post: 830
Upper post cap: 831
Lower post cap: 833
Fascia bracket: 839
Panel clips: 813
Panel: by others

- 13** Handrail moulding: 6935 with 1/4" x 1 1/2" Aluminum flat bar
Center post bracket: 145
Post: 7504
Fascia flange: 7593
Panel clips: 113
Panel: by others
- 14** Handrail moulding: 5235 with 1 1/2" x 1/2" x 1/8" Nickel-Silver channel
Post: 132
Traditional post fascia flange: 198 with Nickel-Silver decorative hex head lag screw
- 15** Spindle: 1/2" Nickel-Silver round bar
Ringed spindle cup: 184